



**CRN TECNOPART, S.A.**




Sant Roc 30  
 08340 VILASSAR DE MAR (Barcelona)  
 Tel 902 404 748 - 937 591 484 Fax 937 591 547  
 e-mail: [crn@crntp.com](mailto:crn@crntp.com) http:// www.crntecnopart.com



**DO-100.07**

**SONDAS Pt100 PARA INSTRUMENTOS PORTÁTILES CON MÓDULO SICRAM**

CÓDIGO	°C MÁX.	TIEMPO REACCIÓN	DIMENSIONES	APLICACIÓN	INSTRUMENTO
TP 472I	-196 +500	3 s			HD2101.1 HD2101.2 HD2103.1 HD2103.2 HD2105.1 HD2105.2 HD2106.1 HD2106.2 HD2156.1 HD2156.2 HD2107.1 HD2107.2 HD2109.1 HD2109.2 HD2114.0 HD2114.2 HD2134.0 HD2134.2 HD2164.0 HD2164.2 HD2114B.0 HD2114B.2 HD2124.1 HD2124.2 HD2127.1 HD2127.2 HD2178.1 HD2178.2 HD2301.0 HD2303.0 HD2304.0 HD2305.0 HD2306.0 HD2307.0
TP473P	-50 +400	5 s			
TP474C	-50 +400	5 s			
TP472I.0	-50 +400	5 s			
TP473P.0	-50 +400	5 s			
TP474C.0	-50 +400	5 s			
TP475A.0	-50 +250	10 s			
TP472I.5	-50 +400	3 s			
TP472I.10	-50 +400	3 s			
TP49A	-70 +400	3,5 s			
TP49AC	-70 +400	5,5 s			
TP49AP	-70 +400	4 s			
TP87	-50 +200	3 s			

CÓDIGO	°C MÁX.	TIEMPO REACCIÓN	DIMENSIONES	APLICACIÓN	INSTRUMENTO
<b>TP87.100</b> <b>(Pt100)</b>  <b>TP87.1000</b> <b>(Pt1000)</b>	-50 +200	3 s			HD2101.1 HD2101.2 HD2103.1 HD2103.2 HD2105.1 HD2105.2 HD2106.1 HD2106.2 HD2156.1 HD2156.2 HD2107.1 HD2107.2 HD2109.1 HD2109.2 HD2114.0 HD2114.2 HD2134.0 HD2134.2 HD2164.0 HD2164.2 HD2114B.0 HD2114B.2 HD2124.1 HD2124.2 HD2127.1 HD2127.2 HD2178.1 HD2178.2 HD2301.0 HD2303.0 HD2304.0 HD2305.0 HD2306.0 HD2307.0
<b>TP47.100</b> <b>(Pt100)</b>  <b>TP47.1000</b> <b>(Pt1000)</b>	-50 +400	3 s			
<b>TP47</b>	Módulo para la conexión directa de sensores Pt100 4 hilos, PT100 3 hilos, Pt1000 2 hilos, y Ni1000 2 hilos		