



CRN TECNOPART, S.A.












Sant Roc 30
08340 VILASSAR DE MAR (Barcelona)
Tel 902 404 748 - 937 591 484 Fax 937 591 547
e-mail: crn@crntp.com http:// www.crntecnopart.com









DO-100.08

SONDAS TERMOPAR TIPO K PARA INSTRUMENTOS PORTÁTILES

CÓDIGO	°C MÁX.	TIEMPO REACCIÓN	DIMENSIONES	APLICACIÓN	INSTRUMENTO
TP741	800	2 s			HD8802 HD8704 HD9016 HD9218 DO9416 DO9847 HD2328 HD2108.1 HD2108.2 HD2128.1 HD2128.2 HD2178.1 HD2178.2 HD2114P.0 HD2114P.2 HD2134P.0 HD2134P.2
TP741/1	400	2 s			
TP741/2	800	2 s			
TP742	800	2 s			
TP742/1	800	2 s			
TP742/2	800	2 s			
TP743	800	3 s			
TP744	400	4 s			
TP745	500	3 s			
TP746	250	2 s			
TP750	1000	3 s			
TP750.0	800	3 s			

CÓDIGO	°C MÁX.	TIEMPO REACCIÓN	DIMENSIONES	APLICACIÓN	INSTRUMENTO
TP751	250	2 s			HD8802 HD8704 HD9016 HD9218 DO9416 DO9847 HD2328 HD2108.1 HD2108.2 HD2128.1 HD2128.2 HD2178.1 HD2178.2 HD2114P.0 HD2114P.2 HD2134P.0 HD2134P.2
TP754	500	2 s			
TP754/9	500	2 s			
TP755	800	2 s			
TP755/9	800	2 s			
TP756	200	2 s			
TP758	400	4 s			
TP772	400	3 s			
TP774	250	2 s			
TP776	400	2 s			
TP777	400	3 s			
TP647 TP647/2 TP647/3 TP648/5	400 400 400 400	2 s 2 s 2 s 2 s			
TP651	1200	6 s			
TP652	1200	6 s			

CÓDIGO	°C MÁX.	TIEMPO REACCIÓN	DIMENSIONES	APLICACIÓN	INSTRUMENTO
TP655	180	2 s			HD8802 HD8704 HD9016 HD9218 DO9416 DO9847 HD2328 HD2108.1 HD2108.2 HD2128.1 HD2128.2 HD2178.1 HD2178.2 HD2114P.0 HD2114P.2 HD2134P.0 HD2134P.2
TP656	400	1 s			
TP656/1	1000	1 s			
TP656/2	1000	1 s			
TP657/1	200	5 s			
TP658	100	1 s			
TP659	500	3 s			
TP660	500	4 s			
TP661	-60 +50	30 s			
CN CS	"K"				
PW	"K"				